



中国国家强制性产品认证证书

证书编号: 2020011002327056

发证日期: 2022年08月23日

有效期至: 2025年09月22日

认证委托人名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

产品生产者名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

生产企业名称 昕诺飞(中国)投资有限公司
及生产地址 上海市闵行区田林路888弄9号楼

产品名称和系列、规格、型号 LED模块用交直流电子控制装置(LED控制装置,内装式,恒流模式,安全特低电压,不可调光,ta: 50°C, tc:80°C, 定温热保护: 110°C)
见附件; 输入: 220-240V~ 50/60Hz; 186-250VDC

产品标准和技术要求 GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求,特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
本证书为变更证书,证书首次颁发日期:2020年09月22日
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn)查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2020011002327056

Valid from: Aug.23,2022

Valid until: Sep.22,2025

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**

Shanghai Minhang District Tianlin Road 888 Lane 9 Building No.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (Built-in, Constant Current Mode, SELV, Non-Dimmable, ta:50°C, tc:80°C, Temperature Declared Thermally Protected: 110°C)
See Appendix; Input: 220-240V ~ 50/60Hz; 186-250VDC

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Sep.22,2020

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

附 录

证书编号: 2020011002327056

第 1 页 共 1 页

纸 号: 3065596

序号	型号	输出电 流 (A)	输出电压 (VDC)	最大输出 电压 (VDCMax)	输出功率 (W)
1	Xitanium 72W 1.2/1.4A 51V DS 230V	1.2	23-51	60	61
		1.4	23-51	60	72
2	Xitanium 54W 0.9/1.05A 51V DS 230V	0.9	23-51	60	46
		1.05	23-51	60	54

输入: 220-240V~, 50/60Hz; 186-250Vdc

注: 此附录与证书同时使用时有效。



中国质量认证中心

