



产品认证证书

证书编号: CQC23010407328

发证日期: 2023年10月11日
有效期至: 2028年10月10日

委托人名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

制造商名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

生产企业名称
及生产地址

产品名称和系列、规格、型号 灯具用电源导轨系统(导轨接合器(II类),集成LED模块用交流电子控制装置, ta: 35°C, tc: 80°C, SELV, 适宜直接安装在普通可燃材料表面)
见附件。220-240V~ 50/60Hz

产品标准和技术要求 GB 17625.1-2022;GB/T 17743-2021;IEC 60570:2019;IEC 60598-1:2017;GB 7000.1-2015

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC12-465431-2018认证规则的要求,特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn)查验证书信息



签发: 谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C 0565246



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC23010407328

Valid from: Oct.11,2023

Valid until:Oct.10,2028

NAME AND REGISTERED ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND LOCATION OF THE FACTORY



PRODUCT NAME, MODEL AND SPECIFICATION

Electrical Supply Track System For Luminaires (Track Coupler (ClassII) , Integrated With A.C. Supplied Electronic Controlgear For LED Modules, ta: 35°C, tc: 80°C, SELV, Suitable For Direct Mounting On Normally Flammable Material)
See Appendix. 220-240V ~ 50/60Hz

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022;GB/T 17743-2021;IEC 60570 : 2019;IEC 60598-1: 2017;GB 7000.1-2015

TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-465431-2018.
The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C 0565246



产品认证证书

证书编号: CQC23010407328

第 1 页 / 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 565246

序号	产品名称	型号	技术参数
1.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V MC 3CG	Fmax. 50N, Uout: 60VdcMax
2.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V MC 3CW	Fmax. 50N, Uout: 60VdcMax
3.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V MC 3CB	Fmax. 50N, Uout: 60VdcMax
4.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V 3CG IA	Fmax. 50N, Uout: 60VdcMax
5.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V 3CW IA	Fmax. 50N, Uout: 60VdcMax
6.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V 3CB IA	Fmax. 50N, Uout: 60VdcMax

220-240V~, 50/60Hz, 导轨接合器 (II类), 集成 LED 模块用交流电子控制装置, ta: 35°C, tc: 80°C, SELV, 适宜直接安装在普通可燃材料表面



中国质量认证中心

