中国国家强制性产品认证证书

证书编号：2020011002356615

认证委托人名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产者名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产企业名称及地址

产品名称和系列、型号、规格

LED 模块用交流电子控制装置（LED 控制装置，整体式，恒流模式，安全特低电压）
见附页；220-240V~ 50/60Hz。

产品标准和技术要求

GB 17625.1-2022;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合《强制性产品认证实施规则 照明电器》（CNCA-C10-01:2014）的要求，特发此证。

发证日期：2024 年 12 月 23 日　　**有效期至：**2025 年 12 月 22 日

本证书为变更证书，证书首次颁发日期：2020 年 12 月 22 日
证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

经中国合格评定国家认可委员会认可 CNAS C001-P

签发：谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2020011002356615

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China

NAME AND LOCATION OF THE FACTORY

PRODUCT NAME,MODEL AND SPECIFICATION

A.C. Supplied Electronic Controlgear For LED Modules (Integral, Constant Current Mode, SELV)
See Appendix；220-240V~ 50/60Hz.

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

Valid from: Dec.23,2024 **Valid until:** Dec.22,2025

Date of original issued: Dec.22,2020

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

SIGNATURE: 谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

中国国家强制性产品认证证书

证书编号：2020011002356615

证书附页：第 1 页 共 1 页

序号	产品型号	输出功率（W）	输出电流（恒流A）	拨码开关选择	
				Pin1	Pin2
1.	Xi 42W/a 0.9-1.05A 40V DS 3C 230V PCB 输出：30-40Vdc，Max.60Vdc	36.0	0.90	ON	ON
		38.0	0.95	OFF	ON
		40.0	1.00	ON	OFF
		42.0	1.05	OFF	OFF
2.	Xi 34W/a 0.7-0.85A 40V DS 3C 230V PCB 输出：30-40Vdc，Max.60Vdc	28.0	0.70	ON	ON
		30.0	0.75	OFF	ON
		32.0	0.80	ON	OFF
		34.0	0.85	OFF	OFF
输入：220-240V～，50/60Hz					

本页为证书附页，应与证书主页同时使用。

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司