



中国国家强制性产品认证证书

证书编号: 2020011002356615

发证日期: 2022年08月11日

有效期至: 2025年12月22日

认证委托人名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

产品生产者名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

生产企业名称
及生产地址

产品名称和系列、规格、型号 LED模块用交流电子控制装置(LED控制装置,整体式,恒流模式,安全特低电压)见附件;220-240V~50/60Hz。

产品标准和技术要求 GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求,特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
本证书为变更证书,证书首次颁发日期:2020年12月22日
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn)查验证书信息



签发: 谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2020011002356615

Valid from: Aug.11,2022

Valid until: Dec.22,2025

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

PRODUCT MODEL(S)

A.C. Supplied Electronic Controlgear For LED Modules (Integral, Constant Current Mode, SELV)
See Appendix; 220-240V~ 50/60Hz.

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Dec.22,2020

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

附 录

证书编号: 2020011002356615

第 1 页 共 1 页

纸 号: 2874347

序号	产品型号	输出功率 (W)	输出电流 (恒流A)	拨码开关选择	
				Pin1	Pin2
1.	Xi 42W/a 0.9-1.05A 40V DS 3C 230V PCB 输出：30-40Vdc， Max. 60Vdc	36.0	0.90	ON	ON
		38.0	0.95	OFF	ON
		40.0	1.00	ON	OFF
		42.0	1.05	OFF	OFF
2.	Xi 34W/a 0.7-0.85A 40V DS 3C 230V PCB 输出：30-40Vdc， Max. 60Vdc	28.0	0.70	ON	ON
		30.0	0.75	OFF	ON
		32.0	0.80	ON	OFF
		34.0	0.85	OFF	OFF

输入：220-240V～，50/60Hz

注: 此附录与证书同时使用时有效。



中国质量认证中心

