



产品认证证书

证书编号: CQC20010279328

申请人名称及地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

制造商名称及地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

生产企业名称及地址

产品名称和系列、规格、型号

灯具用电源导轨系统(导轨接合器(II类),集成LED模块用交流
电子控制装置, $t_a: 35^{\circ}\text{C}$, $t_c: 85^{\circ}\text{C}$, SELV, 适宜直接安装在普通
可燃材料表面)

见附件。220-240V~ 50/60Hz

产品标准和技术要求

GB/T 13961-2008; GB 7000.1-2015

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-465431-2018 认证规则的要求, 特发此证。

发证日期: 2020 年 12 月 22 日

本证书的有效性依据发证机构的定期监督获得保持。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0424496



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC20010279328

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.

Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.

Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE FACTORY

PRODUCT NAME, MODEL AND SPECIFICATION

Electrical Supply Track Systems For Luminaires (Track Coupler (Class II) , Inseparably
Assembled from A.C. Supplied Electronic Controlgear For ED Modules, ta: 35°C, tc: 85°C,
SELV, Suitable For Direct Mounting On Normally Flammable Material)

See Appendix. 220-240V~ 50/60Hz

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 13961-2008;GB 7000.1-2015

TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification
rules of CQC12-465431-2018 .

Valid from: Dec.22,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing
certification body.

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0424496



产品认证证书

附 录

第 1 页 共 2 页

证书编号: CQC20010279328

纸 号: 424496

序号	产品名称	型号	技术参数
1.	导轨接合器	Xi 42W/a 0.9-1.05A 40V DS 3CB 230V	Fmax. 50N, Uout:60VdcMax
2.	导轨接合器	Xi 42W/a 0.9-1.05A 40V DS 3CG 230V	Fmax. 50N, Uout:60VdcMax
3.	导轨接合器	Xi 42W/a 0.9-1.05A 40V DS 3CW 230V	Fmax. 50N, Uout:60VdcMax
4.	导轨接合器	Xi 34W/a 0.7-0.85A 40V DS 3CB 230V	Fmax. 50N, Uout:60VdcMax
5.	导轨接合器	Xi 34W/a 0.7-0.85A 40V DS 3CG 230V	Fmax. 50N, Uout:60VdcMax
6.	导轨接合器	Xi 34W/a 0.7-0.85A 40V DS 3CW 230V	Fmax. 50N, Uout:60VdcMax
7.	导轨接合器	Xi 26W/a 0.5-0.65A 40V DS 3CB 230V	Fmax. 50N, Uout:60VdcMax
8.	导轨接合器	Xi 26W/a 0.5-0.65A 40V DS 3CG 230V	Fmax. 50N, Uout:60VdcMax
9.	导轨接合器	Xi 26W/a 0.5-0.65A 40V DS 3CW 230V	Fmax. 50N, Uout:60VdcMax
10.	导轨接合器	Xi 14W/a 0.2-0.35A 40V DS 3CB 230V	Fmax. 50N, Uout:60VdcMax

注: 此附录与证书同时使用时有效。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 2 页 共 2 页

证书编号: CQC20010279328

纸 号: 424496

序号	产品名称	型号	技术参数
11.	导轨接合器	Xi 14W/a 0.2-0.35A 40V DS 3CG 230V	Fmax. 50N, Uout:60VdcMax
12.	导轨接合器	Xi 14W/a 0.2-0.35A 40V DS 3CW 230V	Fmax. 50N, Uout:60VdcMax

220-240V~ 50/60Hz

注: 此附录与证书同时使用时有效。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>