Australia and New Zealand Certificate of Suitability

Certificate
ULL-104568

Issue date
2026-06-24

Expiration date
2031-06-24

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic controlgear with track adaptor for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability

Certificate No: ULL-104568
Date of Issue/Revision: 2026-06-24

Trade Name or Trademark: PHILIPS, SIGNIFY, ADVANCE, XITANIUM

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:
Rating :
Xitanium 42W/a 0.15-1.05A 42V MC 3CW
Un: 220-240 V, fn: 50/60 Hz, In: 0.25 A, Pn: 50 W, PF: 0.9C,
Irated: 0.15-1.05 A, Prated: 42 W, Uoutput: 10-48 Vdc. Uout: 60 Vdc,
ta: -20…+35 °C, tc: 80 °C, Built-in with double/reinforce insulation, SELV

Xitanium 42W/a 0.15-1.05A 42V MC 3CB
Un: 220-240 V, fn: 50/60 Hz, In: 0.25 A, Pn: 50 W, PF: 0.9C,
Irated: 0.15-1.05 A, Prated: 42 W, Uoutput: 10-48 Vdc. Uout: 60 Vdc,
ta: -20…+35 °C, tc: 80 °C, Built-in with double/reinforce insulation, SELV

Xitanium 42W/a 0.15-1.05A 42V MC 3CG
Un: 220-240 V, fn: 50/60 Hz, In: 0.25 A, Pn: 50 W, PF: 0.9C,
Irated: 0.15-1.05 A, Prated: 42 W, Uoutput: 10-48 Vdc. Uout: 60 Vdc,
ta: -20…+35 °C, tc: 80 °C, Built-in with double/reinforce insulation, SELV

Xitanium 42W/a 0.15-1.05A 42V 3CW IA
Un: 220-240 V, fn: 50/60 Hz, In: 0.25 A, Pn: 50 W, PF: 0.9C,
Irated: 0.15-1.05 A, Prated: 42 W, Uoutput: 10-48 Vdc. Uout: 60 Vdc,
ta: -20…+35 °C, tc: 80 °C, Built-in with double/reinforce insulation, SELV

Xitanium 42W/a 0.15-1.05A 42V 3CB IA
Un: 220-240 V, fn: 50/60 Hz, In: 0.25 A, Pn: 50 W, PF: 0.9C,
Irated: 0.15-1.05 A, Prated: 42 W, Uoutput: 10-48 Vdc. Uout: 60 Vdc,
ta: -20…+35 °C, tc: 80 °C, Built-in with double/reinforce insulation, SELV

Xitanium 42W/a 0.15-1.05A 42V 3CG IA
Un: 220-240 V, fn: 50/60 Hz, In: 0.25 A, Pn: 50 W, PF: 0.9C,
Irated: 0.15-1.05 A, Prated: 42 W, Uoutput: 10-48 Vdc. Uout: 60 Vdc,
ta: -20…+35 °C, tc: 80 °C, Built-in with double/reinforce insulation, SELV

© 2026 UL LLC. All rights reserved.