Australia and New Zealand Certificate of Suitability- addendum

Certificate
ULL-102830-A1

Issue date
2026-06-19

Expiration date
2031-06-19

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

LED DRIVER {component for building in}

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability-addendum

Certificate No: ULL-102830-A1
Original Date of Certification: 2023-01-19
Date of Issue/Revision: 2026-06-19

Trade Name or Trademark: PHILIPS, SIGNIFY, XITANIUM, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared - Commercial (not certified for residential or household use)

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:
Model Rating Information:
Model : Xi SR pW x-yA SNEMP mV Cz sXt
Uin: 220-240 Vac, fn: 50/60 Hz, DC: Iin: 0.55 A max,
Uin: 186-250 Vdc, Iin: 0.4 Adcmax,
Pin: 125 W max, PF: 0.95,
Prated: 110 W max, Irated: 200-1050 mA,
Uout: 35-220 Vdc, Uout(open circuit), 280Vmax,
tc(max): 90°C, ta: -40…+55 °C, Built-in.

Details of model Xi SR pW x-yA SNEMP mV Cz sXt:
p= Rated output power in watt, maximum to 110.
x= Minimum adjustable output current in ampere by simple set, minimum to 0.2, step per 0.01.
y= Maximum adjustable output current in ampere by simple set, maximum to 1.0, step per 0.01.
m= Rated input voltage in volt.
z= 1-3 digits for the size of the housing

Details of addendum :
- Certificate is renewed.
- Trade names "SIGNIFY", "XITANIUM" and "ADVANCE" added.

For NON-IC LED drivers - The requirements of EESS General Guidance Notice 20-007 for NON-IC classified LED drivers is applicable. Refer https://www.eess.gov.au/news-and-notifications/information-and-advisory-notes for more information.

© 2026 UL LLC. All rights reserved.