



# 中国国家强制性产品认证证书

证书编号: 2022181002034184

## 认证委托人名称、地址

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

## 生产者(制造商)名称、地址

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

## 生产企业名称、地址

## 产品名称和系列、型号、规格

LED 模块用交直流电子控制装置(LED 控制装置, 独立式, 恒流模式,  
安全特低电压,  $t_a: 55^{\circ}\text{C}$   $t_c: 85^{\circ}\text{C}$  II 类, IP20, 适宜直接安装在普通可燃材料表面,  
定温热保护:  $110^{\circ}\text{C}$ )  
见附件。220-240V ~ 50/60Hz

## 产品标准和技术要求

GB/T 17743-2021, GB 19510.1-2009, GB 19510.14-2009, GB 17625.1-2012

上述产品符合强制性产品认证实施规则  
CNCA-C10-01: 2014 的要求, 特发此证。

发证日期: 2022 年 07 月 20 日有效期至: 2027 年 07 月 19 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。  
本证书的相关信息可通过认监委网站 [www.cnca.gov.cn](http://www.cnca.gov.cn) 或扫描左下方二维码查询。



邓俊泳

威凯认证检测有限公司



中国·广州·高新技术产业开发区天泰一路3号 (510663)

<http://www.cvc.org.cn>

电话: +86-20-32293722

051682



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. 2022181002034184

## NAME AND ADDRESS OF THE APPLICANT

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

## NAME AND ADDRESS OF THE MANUFACTURER

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

## NAME AND ADDRESS OF THE FACTORY

## NAME, MODEL AND SPECIFICATION

A.C. or D.C Supplied Electronic Controlgear For LED Modules (Controlled Port Dimming, Independent Constant Current SELV ta:55°C tc: 85°C Clas II,IP20 Suitable For Normally Flammable Surfaces ,Temperature Declared Thermally Protected:110°C)  
See Appendix. 220-240V ~ 50/60Hz

## THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 17743-2021,GB 19510.1-2009,GB 19510.14-2009,GB 17625.1-2012

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification (REF NO.CNCA-C10-01: 2014).

**DATE OF ISSUE:** July 20, 2022 **DATE OF EXPIRY:** July 19, 2027

**Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.**

This certificate can be verified through CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn) or the QR code at the lower left.



*Dy Jinyang*



**CVC Certification & Testing Co., Ltd.**

No.3, Tiantaiyi Road, High-tech Industrial Development Zone, Science City, Guangzhou (510663) P. R. China

<http://www.cvc.org.cn>

Tel: +86-20-32293722

051682



# 中国国家强制性产品认证证书

附录:

第 1 页 共 1 页

证书编号: 2022181002034184

纸号: 051682

| 产品型号                                                                                                                                                                                                                                                             | 参数                                                    |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| Xitanium 36W WH 0.3-1.05A 54V SR Is 230V                                                                                                                                                                                                                         | 输出: 0.3-1.05A (恒流可调), Max. 60Vdc;<br>配套Max. 36W LED模块 |
| <p>注:</p> <p>1. 输入: 220-240V~, 50/60Hz, 恒流模式, IP20, ta: 55°C, tc: 85°C, SELV, 独立式, 定温热保护: 110°C, , II类, DALI调光。</p> <p>2. 铭牌上186-250Vdc, I<sub>max</sub>=0.22A, 特指应急照明的输入。</p> |                                                       |

注: 此附录与证书同时使用时有效。

邓俊泳

威凯认证检测有限公司

中国·广州·高新技术产业开发区天泰一路3号 (510663)

<http://www.cvc.org.cn>

电话: +86-20-32293722

