



中国国家强制性产品认证证书

证书编号: 2022181002034185

认证委托人名称、地址

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产者(制造商)名称、地址

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称、地址

产品名称和系列、型号、规格

LED 模块用交直流电子控制装置(LED 控制装置, 内装式, 恒流模式,
安全特低电压, $t_a: 55^{\circ}\text{C}$ $t_c: 85^{\circ}\text{C}$ II 类, IP20, 适宜直接安装在普通可燃材料表面,
定温热保护: 110°C)
见附件。220-240V~ 50/60Hz

产品标准和技术要求

GB/T 17743-2021, GB 19510.1-2009, GB 19510.14-2009, GB 17625.1-2012

上述产品符合强制性产品认证实施规则

CNCA-C10-01: 2014 的要求, 特发此证。

发证日期: 2022 年 07 月 20 日有效期至: 2027 年 07 月 19 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过认监委网站 www.cnca.gov.cn 或扫描左下方二维码查询。



邓俊泳

威凯认证检测有限公司

中国·广州·高新技术产业开发区天泰一路3号 (510663)

<http://www.cvc.org.cn>

电话: +86-20-32293722



051681



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. 2022181002034185

NAME AND ADDRESS OF THE APPLICANT

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

NAME AND ADDRESS OF THE MANUFACTURER

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

NAME AND ADDRESS OF THE FACTORY

NAME, MODEL AND SPECIFICATION

A.C. or D.C Supplied Electronic Controlgear For LED Modules (Controlled Port
Dimming, Built-in Constant Current SELV ta:55°C tc: 85°C Clas II,IP20 Suit
See Appendix. 220-240V ~ 50/60Hz

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 17743-2021,GB 19510.1-2009,GB 19510.14-2009,GB 17625.1-2012

This is to certify that the above mentioned products have met the requirements of
implementation rules for compulsory certification (REF NO.CNCA-C10-01: 2014).

DATE OF ISSUE: July 20, 2022 **DATE OF EXPIRY:** July 19, 2027

**Validity of this certificate is subject to positive result of the regular
follow up inspection by issuing certification body until the expiry date.**

This certificate can be verified through CNCA's website: www.cnca.gov.cn or the QR code at the lower left.



Dy Jinyang



CVC Certification & Testing Co., Ltd.

No.3, Tiantaiyi Road, High-tech Industrial Development Zone, Science City, Guangzhou (510663) P. R. China

<http://www.cvc.org.cn>

Tel: +86-20-32293722

051681



中国国家强制性产品认证证书

附录:

第 1 页 共 1 页

证书编号: 2022181002034185

纸号: 051681

产品型号	参数
Xitanium 36W WH 0.3-1.05A 54V SR Is 230V	输出: 0.3-1.05A (恒流可调), Max. 60Vdc; 配套 Max. 36W LED 模块
注: 1. 输入: 220-240V~, 50/60Hz, 恒流模式, tc: 85°C, 内装式, SELV, 定温热保护: 110°C,  , DALI调光。 2. 铭牌上186-250Vdc, I _{max} =0.22A, 特指应急照明的输入。	

注: 此附录与证书同时使用时有效。

邓俊泳

威凯认证检测有限公司

中国·广州·高新技术产业开发区天泰一路3号 (510663)

<http://www.cvc.org.cn>

电话: +86-20-32293722

