Ref. Certif. No.

NL-126560

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic Control gear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☒ Additional information on page 3
Ratings and principal characteristics	**Product data** Ratings: Xi FP 110W 0.2-0.7A SNLDAE 230V C133 sXt Uin: 220-240 Vac; Iin: 0,55-0,49 Aac; fn: 50/60 Hz, DC; PF: 0,95; Uin: 186-250 Vdc; Iin: 0,39 Adc max; Pin: 121 W; Uoutput: 70-220 Vdc; Uout: 300 Vdc max; Irated: 200-700 mA; Prated: 110 W; ta: -40…+55 °C; tc: 85 °C; built-in; isolating Xi FP 110W .2-.7A SNLDAE 230 C133 TR sXt Uin: 220-240 Vac; In: 0,55-0,49 Aac; Pin: 121 W; fn: 50/60 Hz; PF: 0,95; output voltage: 70-220 Vdc, Uout (open circuit): 300 Vdc max; Iout: 200-700 mA; Pout: 110 W; ta: -40…+55 °C; tc: 85 °C; built-in; isolating Xi FP 110W 0.3-1.0A SNLDAE 230V C133 sXt Uin: 220-240 Vac; Iin: 0,59-0,49 Aac; fn: 50/60 Hz, DC; PF: 0,95; Uin: 186-250 Vdc; Iin: 0,39 Adc max; Pin: 121 W; Uoutput: 50-160 Vdc; Uout: 230 Vdc max; Irated: 300-1050 mA; Prated: 110 W; ta: -40…+55 °C; tc: 85 °C; built-in; isolating Xi FP 110W .3-1A SNLDAE 230 C133 TR sXt Uin: 220-240 Vac; Iin: 0,59-0,49 Aac; Pin: 121 W; fn: 50/60 Hz; PF: 0,95; Uoutput: 50-160 Vdc; Uout: 230 Vdc max; Irated: 300-1050 mA; Prated: 110 W; ta: -40…+55 °C; tc: 85 °C; built-in; isolating
Trademark / Brand (if any)	XITANIUM, ADVANCE, PHILIPS or SIGNIFY

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-08

Signature: Miranda Zhou

Ref. Certif. No.

NL-126560

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xi FP 110W .2-.7A SNLDAE 230 C133 TR sXt, Xi FP 110W .3-1A SNLDAE 230 C133 TR sXt, Xi FP 110W 0.2-0.7A SNLDAE 230V C133 sXt and Xi FP 110W 0.3-1.0A SNLDAE 230V C133 sXt
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	6271280.50 and 6271280.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-08

Signature: Miranda Zhou

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Additional factory

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-08

Signature: Miranda Zhou