



中国国家强制性产品认证证书

证书编号: 2021011002385309

发证日期: 2022年10月17日

有效期至: 2026年06月25日

认证委托人名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

产品生产者名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

生产企业名称
及生产地址

产品名称和系列、规格、型号 LED模块用交直流电子控制装置(LED控制装置,内装式,恒流模式,安全特低电压,ta:50°C,tc:80°C,定温热保护:110°C,不可调光)
见附件;输入:220-240V~50/60Hz;186-250Vdc

产品标准和技术要求 GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求,特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
本证书为变更证书,证书首次颁发日期:2021年06月25日
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn)查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2021011002385309

Valid from: Oct.17,2022

Valid until: Jun.25,2026

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**



PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (LED Controlgear, Built-in, Constant Current Mode, SELV, ta:50°C, tc:80°C, Temperature Declared Thermally Protected: 110°C, Non-Dimmable)
See Appendix; Input: 220-240V~ 50/60Hz; 186-250Vdc

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Jun.25,2021

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

证书编号: 2021011002385309

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3095661

型号	输入功率	输出电流	最大输出 电压	最大输出 功率	拨码开关		
					1	2	3
Xitanium 20W/m 0.15-0.5A 44V DS S 230V	22W	150mA	60Vdc	20W	-	-	
		200mA			-	-	ON
		250mA			-	ON	-
		300mA			-	ON	ON
		350mA			ON	-	-
		400mA			ON	-	ON
		450mA			ON	ON	-
		500mA			ON	ON	ON

输入: 220-240V~ 50/60Hz; 186-250Vdc



中国质量认证中心

