



中国国家强制性产品认证证书

证书编号: 2021011002397521

发证日期: 2022年10月17日

有效期至: 2026年06月25日

认证委托人名称
及注册地址 昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

产品生产者名称
及注册地址 昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

生产企业名称
及生产地址

产品名称和系列、
规格、型号 LED模块用交直流电子控制装置(LED控制装置, 独立式, 恒流模式, 安全特低电压, $t_a: 45^{\circ}\text{C}$, $t_c: 80^{\circ}\text{C}$, II类, IP20, 定温热保护: 110°C , 适宜直接安装在普通可燃材料表面, 不可调光)
见附件; 输入: 220-240V~ 50/60Hz; 186-250Vdc

产品标准和
技术要求 GB 17625.1-2012; GB/T 17743-2021; GB 19510.1-2009; GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
本证书为变更证书, 证书首次颁发日期: 2021年06月25日
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2021011002397521

Valid from: Oct.17,2022

Valid until: Jun.25,2026

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**

PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (LED Controlgear, Independent, Constant Current Mode, SELV, ta:45°C, tc:80°C, Class II, IP20, Temperature Declared Thermally Protected: 110°C, Suitable For Direct Mounting On Normally Flammable Material, Non-Dimmable) See Appendix; Input: 220-240V~ 50/60Hz; 186-250Vdc

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Jun.25,2021

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

证书编号: 2021011002397521

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3095664

序号	型号	输出电流	最大输出 电压	最大输出 功率	拨码开关		
					1	2	3
1	Xitanium 30W/m 0.35-0.7A 44V DS I 230V	350mA	60Vdc	30W	-	-	
		400mA			-	-	ON
		450mA			-	ON	-
		500mA			-	ON	ON
		550mA			ON	-	-
		600mA			ON	-	ON
		650mA			ON	ON	-
		700mA			ON	ON	ON
2	Xitanium 40W/m 0.7-1.05A 44V DS I 230V	700mA	60Vdc	40W	-	-	
		750mA			-	-	ON
		800mA			-	ON	-
		850mA			-	ON	ON
		900mA			ON	-	-
		950mA			ON	-	ON
		1000mA			ON	ON	-
		1050mA			ON	ON	ON

输入: 220-240V~ 50/60Hz; 186-250Vdc



中国质量认证中心

