中国国家强制性产品认证证书

证书编号：2021011002391373

认证委托人名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产者名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产企业名称及地址

产品名称和系列、型号、规格

LED 模块用交流电子控制装置（LED 控制装置，控制端口调光，独立式，恒流模式，安全特低电压，ta:45℃，tc:85℃，II 类，IP20，适宜直接安装在普通可燃材料表面）

见附页。220-240V～ 50/60Hz

产品标准和技术要求

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023

上述产品符合《强制性产品认证实施规则 照明电器》（CNCA-C10-01:2014）的要求，特发此证。

发证日期：2026 年 03 月 19 日　**有效期至：**2031 年 03 月 18 日

本证书为变更证书，证书首次颁发日期：2021 年 05 月 24 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

经中国合格评定国家认可委员会认可 CNAS C001-P

签发：

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2021011002391373

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China

NAME AND LOCATION OF THE FACTORY

PRODUCT NAME,MODEL AND SPECIFICATION

A.C. Supplied Electronic Controlgear For LED Modules (Controlled Port Dimming, Independent, Constant Current Mode, SELV, ta:45℃ , tc:85℃, Class Ⅱ, IP20, Suitable For Direct Mounting On Normally Flammable Material)

See Appendix. 220-240V ~ 50/60Hz

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

Valid from: Mar.19,2026 **Valid until:** Mar.18,2031

Date of original issued: May.24,2021

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

SIGNATURE:

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

中国国家强制性产品认证证书

证书编号：2021011002391373

证书附页：第 1 页 共 1 页

序号	型号	输出参数
1.	Xitanium 44W 0.7-1.05A 42V 1-10V 230V I	输出：Max.60Vdc，0.70A/0.80A/0.90A/1.05A（恒流可调，通过拨码开关调节），配套光源：Max.44W LED 模块

输入：220-240V～，50/60Hz；，，ta:45℃,tc:85℃，SELV，IP20，Ⅱ类，可调光(调光范围：0%-100%,调光方式:输入 1-10Vdc 电压信号调光)，适宜直接安装在普通可燃材料表面

附 拨码开关设置列表：

输入功率	输入电流	输出电流	输出功率	拨码开关位置	
				1	2
34W	0.16A	0.70A	30W	OFF	OFF
38W	0.18A	0.80A	34W	ON	OFF
43W	0.20A	0.90A	38W	OFF	ON
49W	0.23A	1.05A	44W	ON	ON

本页为证书附页，应与证书主页同时使用。

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

http://www.cqc.com.cn 北京市丰台区南四环西路188号九区5号楼 100070 电话：+86 10 83886666