Australia and New Zealand Certificate of Suitability

Certificate
ULL-104585

Issue date
2026-06-29

Expiration date
2031-06-29

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic controlgear for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability

Certificate No: ULL-104585
Date of Issue/Revision: 2026-06-29

Trade Name or Trademark: PHILIPS, SIGNIFY, XITANIUM, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:

Xitanium 75W 0.7-2.0A 54V SR 230V G2
Uin: 220-240 Vac, Iin: 0.38 Aac, fn: 50/60 Hz,
Uin: 186-250 Vdc, Iin: 0.45 Adc, fn: DC
Pin: 84 W, PF: 0.98,
Uoutput: 27-54 Vdc, Uout: 60 Vdc max.,
Irated: 0.7-2.0 A, Prated: 75 W,
ta: -25…+50℃, tc: 75 ℃, SELV, built-in, EL

Xitanium 36W 0.3-1.0A 54V SR 230V G2
Uin: 220-240 Vac, Iin: 0.19 Aac, fn: 50/60 Hz,
Uin: 186-250 Vdc, Iin: 0.23 Adc, fn: DC
Pin: 42 W, PF: 0.98,
Uoutput: 27-54 Vdc, Uout: 60 Vdc max.,
Irated: 0.3-1.0 A, Prated: 36 W,
ta: -25…+50 ℃, tc: 75 ℃, SELV, built-in, EL

© 2026 UL LLC. All rights reserved.