CERTIFICATE

Issued to:
Applicant:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, Netherlands

Licensee:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, Netherlands

Product	:	Electronic controlgear for LED modules
Trade name(s)	:	PHILIPS, SIGNIFY or XITANIUM
Type(s)/model(s)	:	Xi SR 22W 0.2-1.0A SNEMP 230V C123 sXt and Xi SR 40W 0.2-1.0A SNEMP 230V C123 sXt

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:
- a type test according to EN 61347-2-13:2014, EN 61347-2-13:2014/A1:2017, EN 61347-1:2015, EN 61347-1:2015/A1:2021 and EN IEC 62384:2020
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 947556

DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

This certificate is issued on 18 March 2026 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 31-128692 REV.2

DEKRA Certification B.V.

B.T.M. Holtus
Managing Director

Kreny Lin
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL

PRODUCTS
RvA C 001

SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product	:	Electronic controlgear for LED modules
Trade name(s)	:	PHILIPS, SIGNIFY or XITANIUM
Type(s)/model(s)	:	Xi SR 22W 0.2-1.0A SNEMP 230V C123 sXt and Xi SR 40W 0.2-1.0A SNEMP 230V C123 sXt
Rated voltage	:	220-240 Vac or 186-250 Vdc
Nature of supply	:	ac or dc
Rated frequency	:	50/60 Hz at ac
Power factor	:	0,95
Output current	:	200-1050 mA
Ambient temperature (ta)	:	-40…+55 °C
Max case temperature (tc)	:	85°C
Description	:	SELV; Built-in

Product data – type Xi SR 22W 0.2-1.0A SNEMP 230V C123 sXt

Input current	:	0,12-0,11 Aac or 0,09-0.06 Adc
Input power	:	26 W
Output voltage	:	8-48 Vdc
Max output voltage (Uout)	:	60 Vdc
ISR	:	52-60 mA
Output power	:	22 W

Product data – type Xi SR 40W 0.2-1.0A SNEMP 230V C123 sXt

Input current	:	0,2-0,19 Aac or 0,15-0.10 Adc
Input power	:	44 W
Output voltage	:	20-77 Vdc
Max output voltage (Uout)	:	90 Vdc
ISR	:	52-60 mA
Output power	:	40 W

TESTS

Test requirements

EN 61347-2-13:2014
EN 61347-2-13:2014/A1:2017
EN 61347-1:2015
EN 61347-1:2015/A1:2021
EN IEC 62384:2020

Test result

The test results are documented in DEKRA test file 6260939.50 and 6260939.51.

Additional information

Constant current type and with terminal blocks
Used for emergency luminaire excluding high task area
Double/reinforced insulation between input and output
Double/reinforced insulation between input and DALI/Aux terminal
The tests were performed by the manufacturer under the conditions of the agreement concerning the manufacturer's right to conduct type tests for the ENEC certification system under supervision of DEKRA (CTF Stage 3).

This certificate replaces certificate No. 31-128692 REV.1 which we hereby declare invalid.

The list of components is laid down in test report 6260939.50.

Conclusion

The examination has confirmed that all requirements were met.

Factory locations

The factory locations are registered with the numbers 674666 and 306303.