



# CorePro Plastic LEDcandles & lusters



## CorePro candle ND 5-40W E14 827 B35 FR

CorePro, LEDbulb, B35, 40 W, E14, 2700 K, 470 lm, CRI 80, 15000 hour(s), Plastic

The CorePro LEDcandles and lusters are designed for retrofit replacement of incandescent lamps and are particularly attractive for chandeliers. They are compatible with fixtures with an E14 holder for candles and E14 or E27 holders for lusters and are available in multiple color temperatures. LED lamps deliver huge energy savings of up to 80% energy-saving compared with halogen lamps and provide excellent quality of light. By offering a lifetime of 15,000 hours it lowers maintenance costs. The CorePro LED candles and lusters are perfect for your basic lighting needs.

### Product data

General Information		Color Consistency	
Cap-Base	E14	Color Consistency	<6
Nominal lifetime	15,000 hour(s)	Color rendering index (CRI)	80
Switching Cycle	50,000	LLMF At End Of Nominal Lifetime (Nom)	70 %
Lighting Technology	LEDbulb	Photobiological safety according to EN 62471	RG1
Warranty period	2 years	<b>Operating and Electrical</b>	
<b>Light Technical</b>		Line Frequency	50 to 60 Hz
Color Code	827 [CCT of 2700K]	Input Frequency	50 to 60 Hz
Luminous Flux	470 lm	Power Consumption	5 W
Color Designation	Warm White (WW)	Lamp Current (Nom)	44 mA
Correlated Color Temperature (Nom)	2700 K	Wattage Equivalent	40 W
Luminous Efficacy (rated) (Nom)	94.00 lm/W	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s

## CorePro Plastic LEDcandles & lusters

Power Factor (Fraction)	0.51
Voltage (Nom)	220-240 V

### Temperature

T-Case Maximum (Nom)	81 °C
----------------------	-------

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	B35
Net Weight (Piece)	0.040 kg

### Approval and Application

Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	453199
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


### Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

### Product Data

Order product name	CorePro candle ND 5-40W E14 827 B35 FR
Full product name	CorePro candle ND 5-40W E14 827 B35 FR
Full product code	871951431250000
Order code	929002968402
Material Nr. (12NC)	929002968402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514312500
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514312517

## Dimensional drawing



Product	D	C
CorePro candle ND 5-40W E14 827 B35 FR	45 mm	87 mm



## CorePro Plastic LEDcandles & lusters

