



# CorePro Plastic LEDcandles & lusters

## CorePro lustre ND 7-60W E14 827 P48 FR

CorePro, LEDbulb, P48, 60 W, E14, 2700 K, 806 lm, CRI 80, 15000 hour(s), Plastic

CorePro, LEDbulb, P48, 60 W, E14, 2700 K, 806 lm, CRI 80, 15000 hour(s), Plastic, 115.00 lm/W, EEL E, PF 0.51, RG1, IP20, SVM 0.4, PstLM 1

### Product data

General Information	
Cap-Base	E14
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	2 years
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	115.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	7 W
Lamp Current (Nom)	59 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	87 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

# CorePro Plastic LEDcandles & lusters

Bulb Material	Plastic
Bulb Shape	P48
Net Weight (Piece)	0.023 kg

## Approval and Application

Energy Efficiency Class	E
Energy Consumption kWh/1000 h	7 kWh
EPREL Registration Number	453214
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C

## Application Conditions


can it be used in closed luminaires	No
-------------------------------------	----

Wireless Technology	Not applicable
---------------------	----------------

## Product Data


Order product name	CorePro lustre ND 7-60W E14 827 P48 FR
Full product name	CorePro lustre ND 7-60W E14 827 P48 FR
Full product code	871951431304000
Order code	929002973102
Material Nr. (12NC)	929002973102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514313040
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514313057

## Dimensional drawing




Product	D	C
CorePro lustre ND 7-60W E14 827 P48 FR	48 mm	93 mm

## Photometric data




Light Distribution Diagram - CorePro lustre ND 7-60W E14 827 P48 FR



Spectral Power Distribution Colour - CorePro lustre ND 7-60W E14 827 P48 FR

# CorePro Plastic LEDcandles & lusters


## Photometric data




Technical Parameters 43 Philips Lighting B.V. Page 10

General uniform lighting - CorePro lustre ND 7-60W E14 827 P48 FR

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro lustre ND 7-60W E14 827 P48 FR

