

MASTER Value Decorative LED bulbs

MAS VLE LEDBulbD4-25W E27 ST64 GOLD SP G

MASTER Value, LEDbulb, ST64, 25 W, E27, 1800 K, 250 lm, CRI 80, 15000 hour(s), Glass

MASTER Value, LEDbulb, ST64, 25 W, E27, 1800 K, 250 lm, CRI 80, 15000 hour(s), Glass, 62 lm/W, PF 0.7, RG1, IP20, SVM 0.4, PstLM 1

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Warranty period	2.5 years

Light Technical	
Color Code	818 [CCT of 1800K]
Luminous Flux	250 lm
Color Designation	1800
Correlated Color Temperature (Nom)	1800 K
Luminous Efficacy (rated) (Nom)	62 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	35 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Amber

MASTER Value Decorative LED bulbs

Bulb Material	Glass
Bulb Shape	ST64
Net Weight (Piece)	0.048 kg

Approval and Application

Energy Consumption kWh/1000 h	4 kWh
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C

Application Conditions

can it be used in closed luminaires	No

Wireless Technology	Not applicable

Product Data

Order product name	MAS VLE LEDBulbD4-25W E27 ST64 GOLD SP G
Full product name	MAS VLE LEDBulbD4-25W E27 ST64 GOLD SP G
Full product code	871951431553200
Order code	929002982902
Material Nr. (12NC)	929002982902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514315532
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514315549

Dimensional drawing



Product	D	C
MAS VLE LEDBulbD4-25W E27 ST64 GOLD SP G	65 mm	143 mm

Photometric data

Spectral Power Distribution Colour - MAS VLE LEDBulbD4-25W E27 ST64 GOLD SP G

Light Distribution Diagram - MAS VLE LEDBulbD4-25W E27 ST64 GOLD SP G

MASTER Value Decorative LED bulbs

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS VLE LEDBulbD4-25W E27 ST64 GOLD SP G

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.