



Master Value Decorative LED candles and lusters

MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G

MASTER Value, LEDbulb, B35, 15 W, E14, 1800 K, 136 lm, CRI 80, 15000 hour(s), Glass

The new Deco collection (candles and lusters) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

Product data

General Information	
Cap-Base	E14
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Warranty period	2.5 years
Light Technical	
Color Code	818 [CCT of 1800K]
Luminous Flux	136 lm
Color Designation	1800
Correlated Color Temperature (Nom)	1800 K
Luminous Efficacy (rated) (Nom)	54 lm/W

Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	2.5 W
Lamp Current (Nom)	14 mA
Wattage Equivalent	15 W
Starting Time (Nom)	0.5 s

Master Value Decorative LED candles and lusters

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	38 °C
----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Amber
Bulb Material	Glass
Bulb Shape	B35
Net Weight (Piece)	0.020 kg

Approval and Application

Energy Consumption kWh/1000 h	3 kWh
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data

Order product name	MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G
Full product name	MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G
Full product code	871951431603400
Order code	929002983202
Material Nr. (12NC)	929002983202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514316034
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514316041

Dimensional drawing



Product	D	C
MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G	36 mm	95 mm



Master Value Decorative LED candles and lusters

Photometric data

Light Distribution Diagram - MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G

Spectral Power Distribution Colour - MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G

