



Master Value Decorative LED candles and lusters

MAS VLE LEDLusterD 2.6-15W E14 P45 SP G

MASTER Value, LEDbulb, P45, 15 W, E14, 1800 K, 136 lm, CRI 80, 15000 hour(s), Glass

The new Deco collection (candles and lusters) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

Product data

General Information		Color Consistency	
Cap-Base	E14	Color rendering index (CRI)	80
Nominal lifetime	15,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)	70 %
Switching Cycle	20,000	Photobiological safety according to EN 62471	RG1
Lighting Technology	LEDbulb	Operating and Electrical	
Warranty period	2.5 years	Line Frequency	50 to 60 Hz
Light Technical		Input Frequency	50 to 60 Hz
Color Code	818 [CCT of 1800K]	Power Consumption	2.6 W
Luminous Flux	136 lm	Lamp Current (Nom)	14 mA
Color Designation	1800	Wattage Equivalent	15 W
Correlated Color Temperature (Nom)	1800 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	52 lm/W	Warm-up time to 60% light	0.5 s

Master Value Decorative LED candles and lusters

Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	38 °C
----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Amber
Bulb Material	Glass
Bulb Shape	P45
Net Weight (Piece)	0.014 kg

Approval and Application

Energy Consumption kWh/1000 h	3 kWh
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data

Order product name	MAS VLE LEDLusterD 2.6-15W E14 P45 SP G
Full product name	MAS VLE LEDLusterD 2.6-15W E14 P45 SP G
Full product code	871951431605800
Order code	929002983302
Material Nr. (12NC)	929002983302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514316058
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514316065

Dimensional drawing



Product	D	C
MAS VLE LEDLusterD 2.6-15W E14 P45 SP G	46 mm	80 mm



Master Value Decorative LED candles and lusters

Photometric data

Spectral Power Distribution Colour - MAS VLE LEDLusterD 2.6-15W E14 P45 SP G

Light Distribution Diagram - MAS VLE LEDLusterD 2.6-15W E14 P45 SP G

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - MAS VLE LEDLusterD 2.6-15W E14 P45 SP G

