

Classic filament LED bulbs

4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF

LEDbulb, ST19, 40 W, E26, 2000 K, 300 lm, 15000 hour(s)

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	820 [CCT of 2000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	300 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	68.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	4.4 W
Lamp Current (Nom)	50 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Amber
Bulb Shape	ST19
UL Wet/ damp/ dry location	Wet location

Classic filament LED bulbs

Net Weight (Piece)	0.044 kg
--------------------	----------

Approval and Application

EU RoHS compliant	Yes
T20 compliant	N/A
Ambient temperature range	-20 °C to 45 °C

Application Conditions


can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF
--------------------	--------------------------------------


Full product name	4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF
Order code	929002990303
Material Nr. (12NC)	929002990303
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	046677564841
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677564846

Dimensional drawing




Product	D	C
4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF	64 mm	137 mm

Photometric data




Light Distribution Diagram - 4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF



Spectral Power Distribution Colour - 4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF

Classic filament LED bulbs

Photometric data




General Parameters 4.1
Photometry 4.1
Page 11

General uniform lighting - 4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF

