



# LED Lamps

## LEDBulb 6W B22 965 230V 2PF/3 AU

LEDbulb, A60S, 65 W, B22, 6500 K, 700 lm, 25000 h, Plastic

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

### Product data

General Information	
Cap-Base	B22
Nominal lifetime	25,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LEDbulb
Light Technical	
Color Code	965 [CCT of 6500K]
Color Code	965 [CCT of 6500K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	700 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	116 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	6 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	110 mm

## LED Lamps

Overall width	60 mm
Overall height	110 mm
Dimensions (Height x Width x Depth)	110 x 60 x 110 mm
Bulb Shape	A60S
Net Weight (Piece)	0.042 kg

### Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


### Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

### Product Data

Order product name	LEDBulb 6W B22 965 230V 2PF/3 AU
Full product name	LEDBulb 6W B22 965 230V 2PF/3 AU
Full product code	871869968798400
Local code description	EB6A60c865NC2
Order code	929003006819
Material Nr. (12NC)	929003006819
Local order code	EB6A60C865NC2
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8718699687984
Numerator - Packs per outer box	3
EAN/UPC - Case	8718699687991


## Dimensional drawing




### Product

LEDBulb 6W B22 965 230V 2PF/3 AU

## Photometric data




Light Distribution Diagram - LEDBulb 6W B22 965 230V 2PF/3 AU



Spectral Power Distribution Colour - LEDBulb 6W B22 965 230V 2PF/3 AU

# LED Lamps


## Photometric data




General of Parameters 43 Philips Lighting B.V. Page 107

General uniform lighting - LEDBulb 6W B22 965 230V 2PF/3 AU

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 6W B22 965 230V 2PF/3 AU

