



# LED Lamps

## LEDBulb 10W E27 930 230V 2PF/3 AU

LEDbulb, A60M, 89 W, E27, 3000 K, 1150 lm, 25000 h, Plastic

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LEDBulb

Light Technical	
Color Code	930 [CCT of 3000K]
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,150 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	85 mA
Wattage Equivalent	89 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	110 mm

## LED Lamps

Overall width	60 mm
Overall height	110 mm
Dimensions (Height x Width x Depth)	110 x 60 x 110 mm
Bulb Shape	A60M
Net Weight (Piece)	0.042 kg

### Approval and Application


EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C

### Product Data

Order product name	LEDBulb 10W E27 930 230V 2PF/3 AU
--------------------	-----------------------------------


Full product name	LEDBulb 10W E27 930 230V 2PF/3 AU
Full product code	871869968808000
Local code description	EB10A60a830NC2
Order code	929003007519
Material Nr. (12NC)	929003007519
Local order code	EB10A60A830NC2
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8718699688080
Numerator - Packs per outer box	3
EAN/UPC - Case	8718699688097

## Dimensional drawing




Product	D	C
LEDBulb 10W E27 930 230V 2PF/3 AU	60 mm	110 mm

## Photometric data




Spectral Power Distribution Colour - LEDBulb 10W E27 930 230V 2PF/3 AU



Light Distribution Diagram - LEDBulb 10W E27 930 230V 2PF/3 AU

# LED Lamps

## Photometric data




General of Parameters 41 Philips Lighting B.V. Page 117

General uniform lighting - LEDBulb 10W E27 930 230V 2PF/3 AU

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 10W E27 930 230V 2PF/3 AU

