



MASTER Glass LED bulbs

MAS LEDBulbDT5.9-60W E27 927A60CL G

MASTER, LEDbulb, A60, 60 W, E27, 2200 K, 2700 K, 806 lm, CRI 90, 25000 hour(s), Glass

MASTER, LEDbulb, A60, 60 W, E27, 2200 K, 2700 K, 806 lm, CRI 90, 25000 hour(s), Glass, 136 lm/W, EEL D, PF 0.6, RG0, IP65, SVM 0.4, PstLM 0.9

Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	5 years
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Luminous Flux	806 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	136 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5.9 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear

MASTER Glass LED bulbs

Bulb Material	Glass
Bulb Shape	A60
Net Weight (Piece)	0.030 kg

Approval and Application

Energy Efficiency Class	D
Energy Consumption kWh/1000 h	6 kWh
EPREL Registration Number	1109131
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.9
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 °C to 45 °C

Application Conditions


can it be used in closed luminaires	No
-------------------------------------	----

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	MAS LEDBulbDT5.9-60W E27 927A60CL G
Full product name	MAS LEDBulbDT5.9-60W E27 927A60CL G
Full product code	871951444971800
Order code	929003010382
Material Nr. (12NC)	929003010382
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514449718
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514449725

Dimensional drawing




Product	D	C
MAS LEDBulbDT5.9-60W E27 927A60CL G	60 mm	104 mm

Photometric data




Spectral Power Distribution Colour - MAS LEDBulbDT5.9-60W E27 927A60CL G



Light Distribution Diagram - MAS LEDBulbDT5.9-60W E27 927A60CL G

MASTER Glass LED bulbs

Photometric data



General uniform lighting - MAS LEDBulbDT5.9-60W E27 927A60CL G

General uniform lighting - MAS LEDBulbDT5.9-60W E27 927A60CL G

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDBulbDT5.9-60W E27 927A60CL G

