

MASTER GLASS LED candles and lustres

MAS LEDCandleDT3.4-40WE14 927B35CLGUK

MASTER, LEDbulb, B35, 40 W, E14, 2200 K, 2700 K, 470 lm, CRI 90, 25000 h, Glass

MASTER, LEDbulb, B35, 40 W, E14, 2200 K, 2700 K, 470 lm, CRI 90, 25000 h, Glass, 138 lm/W, EEL D, PF 0.6, RG0, IP65, SVM 0.4, PstLM 0.9

Product data

General Information	
Cap base	E14
Nominal lifetime	25,000 h
Switching Cycle	20,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	5 years
Light Technical	
Colour Code	922-927 [CCT of 2200K-2700K]
Luminous Flux	470 lm
Colour designation	Warm Glow (WG)
Correlated Colour Temperature (Nom)	2200 2700 K
Luminous efficacy (rated) (nom.)	138 lm/W
Colour consistency	<6
Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %

Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	3.4 W
Lamp current (nom.)	24 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	70 °C

MASTER GLASS LED candles and lustres

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Lamp Finish	Clear
Bulb material	Glass
Bulb shape	B35
Net Weight (Piece)	0.013 kg

Approval and Application

Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	4 kWh
EPREL Registration Number	1109139
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	0.9
Stroboscopic effect	0.4
Ambient temperature range	-20°C to 45°C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	MAS LEDCandleDT3.4-40WE14 927B35CLGUK
Full product name	MAS LEDCandleDT3.4-40WE14 927B35CLGUK
Full EOC	871951446661600
Order code	929003012242
Material no. (12 NC)	929003012242
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514466616
Numerator – packs per outer box	10
EAN/UPC – Case	8719514466623

Dimensional drawing




Product	D	C
MAS LEDCandleDT3.4-40WE14 927B35CLGUK	35 mm	97 mm

Photometric data




Light Distribution Diagram - MAS LEDCandleDT3.4-40WE14 927B35CLGUK



Spectral Power Distribution Colour - MAS LEDCandleDT3.4-40WE14 927B35CLGUK

MASTER GLASS LED candles and lustres

Photometric data




General Uniform Lighting - MAS LEDCandleDT3.4-40WE14 927B35CLGUK

General uniform lighting - MAS LEDCandleDT3.4-40WE14 927B35CLGUK

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDCandleDT3.4-40WE14 927B35CLGUK

