



Classic filament LED candles and lusters

LEDclassic 3.5W B35 2700K E14 D CL AU

LEDbulb, B35, 40 W, E14, 2700 K, 470 lm, 15000 hour(s), Glass

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information		LLMF At End Of Nominal Lifetime (Nom)	
Cap-Base	E14		70 %
Nominal lifetime	15,000 hour(s)	Operating and Electrical	
Switching Cycle	20,000	Input Frequency	50 to 60 Hz
Rated Lifetime (Hours)	15,000 hour(s)	Power Consumption	3.5 W
Lighting Technology	LEDbulb	Lamp Current (Nom)	24 mA
Light Technical		Wattage Equivalent	40 W
Color Code	927 [CCT of 2700K]	Starting Time (Nom)	0.5 s
Color Code	927 [CCT of 2700K]	Warm-up time to 60% light	0.5 s
Beam Angle (Nom)	300 degree(s)	Power Factor (Fraction)	0.6
Luminous Flux	470 lm	Voltage (Nom)	220-240 V
Color Designation	Warm White (WW)	Temperature	
Correlated Color Temperature (Nom)	2700 K	T-Case Maximum (Nom)	70 °C
Luminous Efficacy (rated) (Nom)	134 lm/W		
Color Consistency	<6		
Color rendering index (CRI)	90		

Classic filament LED candles and lusters

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Overall length	97 mm
Overall width	35 mm
Overall height	97 mm
Dimensions (Height x Width x Depth)	97 x 35 x 97 mm
Bulb Shape	B35
Net Weight (Piece)	0.014 kg

Approval and Application

Energy Consumption kWh/1000 h	4 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

Ambient temperature range	-20 to +45 °C
---------------------------	---------------


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	LEDclassic 3.5W B35 2700K E14 D CL AU
Full product name	LEDclassic 3.5W B35 2700K E14 D CL AU
Full product code	871951437729500
Order code	929003012279
Material Nr. (12NC)	929003012279
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514377295
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514377301

Dimensional drawing




Product	D	C
LEDclassic 3.5W B35 2700K E14 D CL AU	35 mm	97 mm

Photometric data




Light Distribution Diagram - LEDclassic 3.5W B35 2700K E14 D CL AU



Spectral Power Distribution Colour - LEDclassic 3.5W B35 2700K E14 D CL AU

Classic filament LED candles and lusters

Photometric data



General uniform lighting - LEDclassic 3.5W B35 2700K E14 D CL AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDclassic 3.5W B35 2700K E14 D CL AU

