



Classic filament LED bulbs

LEDClassic 8W A19 E27 850 CL ND 1PF/10

LEDbulb, A19, 60 W, E27, 5000 K, 800 lm, 15000 hour(s)

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Warranty period	1 years

Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux	800 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8 W
Lamp Current (Nom)	110 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	55 °C

Controls and Dimming	
Dimmable	No

Classic filament LED bulbs

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	A19
Net Weight (Piece)	0.090 kg

Approval and Application

EU RoHS compliant	Yes
Ambient temperature range	-20 to +40 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	LEDClassic 8W A19 E27 850 CL ND 1PF/10
Full product name	LEDClassic 8W A19 E27 850 CL ND 1PF/10
Order code	929003068142
Material Nr. (12NC)	929003068142
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677571948
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677571943

Dimensional drawing




Product	D	C
LEDClassic 8W A19 E27 850 CL ND 1PF/10	60 mm	106 mm

Photometric data




Spectral Power Distribution Colour - LEDClassic 8W A19 E27 850 CL ND 1PF/10



Light Distribution Diagram - LEDClassic 8W A19 E27 850 CL ND 1PF/10

Classic filament LED bulbs

Photometric data




General Parameters 43 Philips Lighting B.V. Page 10

General uniform lighting - LEDClassic 8W A19 E27 850 CL ND 1PF/10

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDClassic 8W A19 E27 850 CL ND 1PF/10

