



# Classic filament LED candles and lusters

## LEDClassic 4.5W B11 E12 850 CL ND 1PF/10

LEDbulb, B11, 40 W, E12, 5000 K, 500 lm, 15000 hour(s)

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	E12
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Warranty period	1 years
Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux	500 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	111.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	4.5 W
Lamp Current (Nom)	75 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No

# Classic filament LED candles and lusters

## Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	B11
Net Weight (Piece)	0.014 kg

## Approval and Application

EU RoHS compliant	Yes
Ambient temperature range	-20 to +40 °C


## Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

## Product Data


Order product name	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10
Full product name	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10
Order code	929003068442
Material Nr. (12NC)	929003068442
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677571979
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677571974

## Dimensional drawing




Product	D	C
LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	35 mm	99 mm

## Photometric data



Spectral Power Distribution Colour - LEDClassic 4.5W B11 E12 850 CL ND 1PF/10



Light Distribution Diagram - LEDClassic 4.5W B11 E12 850 CL ND 1PF/10

