



Candle LED

LEDLuster 6W P45 6500K E27 ND FR AU 2CT

LEDbulb, P45, 60 W, E27, 6500 K, 620 lm, 15000 hour(s), Plastic

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb
Light Technical	
Color Code	865 [CCT of 6500K]
Color Code	865 [CCT of 6500K]
Luminous Flux	620 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	103 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	6 W
Lamp Current (Nom)	51 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	83 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	87 mm

Candle LED

Overall width	45 mm
Overall height	87 mm
Dimensions (Height x Width x Depth)	87 x 45 x 87 mm
Bulb Shape	P45
Net Weight (Piece)	0.021 kg

Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	LEDLuster 6W P45 6500K E27 ND FR AU 2CT
Full product name	LEDLuster 6W P45 6500K E27 ND FR AU 2CT
Full product code	871951437443000
Order code	929003095679
Material Nr. (12NC)	929003095679
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8719514374430
Numerator - Packs per outer box	3
EAN/UPC - Case	8719514374447

Dimensional drawing



Product	D	C
LEDLuster 6W P45 6500K E27 ND FR AU 2CT	45 mm	87 mm

Photometric data




General uniform lighting - LEDLuster 6W P45 6500K E27 ND FR AU 2CT

Spectral Power Distribution Colour - LEDLuster 6W P45 6500K E27 ND FR AU 2CT

Candle LED

Photometric data



Light Distribution Diagram - LEDLuster 6W P45 6500K E27 ND FR AU 2CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDLuster 6W P45 6500K E27 ND FR AU 2CT

