

Classic filament LED bulbs

LEDclassic 6W B22 2700K G120 D CL AU

LEDbulb, G120, 60 W, B22, 2700 K, 806 lm, 15000 hour(s), Glass

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	B22
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb
Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	134 lm/W
Color Consistency	<6
Color rendering index (CRI)	90

LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	6 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers

Classic filament LED bulbs

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Overall length	178 mm
Overall width	124 mm
Overall height	178 mm
Dimensions (Height x Width x Depth)	178 x 124 x 178 mm
Bulb Shape	G120
Net Weight (Piece)	0.165 kg


Approval and Application

Energy Consumption kWh/1000 h	6 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

Product Data



Order product name	LEDclassic 6W B22 2700K G120 D CL AU
Full product name	LEDclassic 6W B22 2700K G120 D CL AU
Full product code	871951438590000
Order code	929003100779
Material Nr. (12NC)	929003100779
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514385900
Numerator - Packs per outer box	3
EAN/UPC - Case	8719514385917

Dimensional drawing



Product	D	C
LEDclassic 6W B22 2700K G120 D CL AU	124 mm	178 mm

Photometric data




General uniform lighting - LEDclassic 6W B22 2700K G120 D CL AU

Light Distribution Diagram - LEDclassic 6W B22 2700K G120 D CL AU


Classic filament LED bulbs

Photometric data




Spectral Power Distribution Colour - LEDclassic 6W B22 2700K G120 D CL AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDclassic 6W B22 2700K G120 D CL AU

