



# Deep Recessed Spotlight

## RS350 G2 RC Rd D55 7W 30K 24D 1H

Deep Recessed offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance, especially the anti glare feature.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Nominal lifetime	25,000 hour(s)
Switching Cycle	15,000
Lighting Technology	LED
Value ladder	Performance
Warranty period	1 years

Light Technical	
Luminous Flux	540 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	77.14 lm/W
Color rendering index (CRI)	90
Light source color	930 warm white
Optic type	Beam angle 36°
Luminaire light beam spread	24°

Operating and Electrical	
Input Voltage	220 to 240 V

Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Inrush current	8.5 A
Inrush time	0.18 ms
Power Consumption	7 W
Warm-up time to 60% light	<2 s
Power Factor (Fraction)	0.5
Connection	Flying leads/wires
Cable	Cable 0.7 m without plug
Number of products on MCB of 16 A type B	110
Suitable for random switching	No
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum die-cast
Reflector material	Polycarbonate aluminum coated

# Deep Recessed Spotlight

Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Gray
Optical cover finish	Clear
Overall height	67 mm
Overall diameter	63 mm
Net weight	0.16 kg
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	0.160 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Warranty	3 year(s)
EyeComfort	Yes
Ambient temperature range	-20 to +40 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.4369, 0.404) 5SDCM
Power consumption tolerance	+/-10%


## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.015 %
Median useful life L70B50	25,000 hour(s)


## Product Data

Order product name	RS350 G2 RC Rd D55 7W 30K 24D 1H
Full product name	RS350 G2 RC Rd D55 7W 30K 24D 1H
Full product code	692234195760400
Order code	929003215010
Material Nr. (12NC)	929003215010
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341957604
Numerator - Packs per outer box	12
EAN/UPC - Case	6922341957611


## Dimensional drawing



## Photometric data



Light Distribution Diagram - RS350 G2 RC Rd D55 7W 30K 24D 1H



Accent Lighting Spots - RS350 G2 RC Rd D55 7W 30K 24D 1H

## Deep Recessed Spotlight

