



Meson Downlight

59443 Plus MESON 080 7W 40K WH KR

Meson Downlight, 7 W, 550 lm, 4000 K, Wide beam, White

Plastic, White, Power supply unit, 550 lm, 7 W, 78 lm/W, 4000 K, (0.3818, 0.3797) 6SDCM, Wide beam, Opal, Polycarbonate, IP20 | Finger-protected, IK03 | 0.3 J, Safety class II, Flying leads/wires

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Switching Cycle	7,500
Warranty period	1 years

Light Technical	
Luminous Flux	550 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	78 lm/W
Color rendering index (CRI)	80
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	110°
Photobiological safety according to EN 62471	RG0

Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 or 60 Hz
Inrush current	5 A

Inrush time	0.17 ms
Power Consumption	7 W
Power Factor (Fraction)	0.5
Connection	Flying leads/wires
Cable	Cable without plug 2-pole
Number of products on MCB of 16 A type B	190
Suitable for random switching	Not applicable
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit
Constant light output	No

Mechanical and Housing	
Housing Material	Plastic
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White

Meson Downlight

Optical cover finish	Opal
Overall height	45.5 mm
Overall diameter	105 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	0.050 kg

Approval and Application

Insulation Coverage Rating	Non IC Rating
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+15%/-5%
-------------------------	----------

Initial chromaticity	(0.3818, 0.3797) 6SDCM
Power consumption tolerance	+/-10%



Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	5
Median useful life L70B50	15,000 hour(s)



Product Data

Order product name	59443 Plus MESON 080 7W 40K WH KR
Full product name	59443 Plus MESON 080 7W 40K WH KR
Full product code	872016924981300
Order code	929003304508
Material Nr. (12NC)	929003304508
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169249813
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169249820

Dimensional drawing



Photometric data



Light Distribution Diagram - 59443 Plus MESON 080 7W 40K WH KR

General uniform lighting - 59443 Plus MESON 080 7W 40K WH KR

Meson Downlight

