



# Deep Recessed Spotlight

## RS350 G2 RC Rd D75 7W 27K 24D 1H

Deep Recessed Spotlight, 7 W, 530 lm, 2700 K, Dark gray

Deep Recessed offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance, especially the anti glare feature.

### Product data

General Information	
Light source replaceable	No
Light source engine type	LED
Warranty period	1 years
Light Technical	
Luminous Flux	530 lm
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color rendering index (CRI)	90
Light source color	927 warm white
Luminaire light beam spread	24°
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 or 60 Hz
Input Frequency	- Hz
Inrush current	8.5 A
Power Consumption	7 W

Power Factor (Fraction)	0.5
Number of products on MCB of 16 A type B	110
Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	No
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die-cast
Reflector material	-
Housing Color	Dark gray
Overall height	80 mm
Overall diameter	84 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Net Weight (Piece)	0.250 kg

# Deep Recessed Spotlight

## Approval and Application

Insulation Coverage Rating	Non IC Rating
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Ambient temperature range	-20 to +40 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%


## Over Time Performance (IEC Compliant)

Median useful life L70B50	25,000 hour(s)
---------------------------	----------------



## Product Data

Order product name	RS350 G2 RC Rd D75 7W 27K 24D 1H
Full product name	RS350 G2 RC Rd D75 7W 27K 24D 1H
Full product code	694197060355300
Order code	929003340210
Material Nr. (12NC)	929003340210
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6941970603553
Numerator - Packs per outer box	12
EAN/UPC - Case	6941970603560

## Dimensional drawing



## Photometric data



Accent Lighting Spots - RS350 G2 RC Rd D75 7W 27K 24D 1H

Light Distribution Diagram - RS350 G2 RC Rd D75 7W 27K 24D 1H

## Deep Recessed Spotlight

