



Deep Recessed Spotlight

RS350 G2 RC Rd D75 7W 35K 36D 1H

Deep Recessed Spotlight, 7 W, 580 lm, 3500 K, Dark gray

Deep Recessed offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance, especially the anti glare feature.

Product data

General Information			
Light source replaceable	No	Inrush current	8.5 A
Nominal lifetime	25,000 hour(s)	Power Consumption	7 W
Light source engine type	LED	Warm-up time to 60% light	<2 s
Switching Cycle	15,000	Power Factor (Fraction)	0.5
Warranty period	1 years	Number of products on MCB of 16 A type B	110
		Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	580 lm	Dimmable	No
Correlated Color Temperature (Nom)	3500 K	Constant light output	No
Luminous Efficacy (rated) (Nom)	82 lm/W		
Color rendering index (CRI)	90	Mechanical and Housing	
Light source color	935 warm white	Housing Material	Aluminum die-cast
Luminaire light beam spread	36°	Reflector material	-
		Housing Color	Dark gray
Operating and Electrical		Overall height	80 mm
Input Voltage	220 V	Overall diameter	84 mm
Line Frequency	50 or 60 Hz	Net weight	0.25 kg
Input Frequency	- Hz	Ingress protection code	IP20 [Finger-protected]

Deep Recessed Spotlight

Mech. impact protection code	-
Net Weight (Piece)	0.250 kg

Approval and Application

Insulation Coverage Rating	Non IC Rating
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Warranty	3 year(s)
EyeComfort	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%


Over Time Performance (IEC Compliant)

Median useful life L70B50	25,000 hour(s)
---------------------------	----------------



Product Data

Order product name	RS350 G2 RC Rd D75 7W 35K 36D 1H
Full product name	RS350 G2 RC Rd D75 7W 35K 36D 1H
Full product code	694197060361400
Order code	929003343510
Material Nr. (12NC)	929003343510
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6941970603614
Numerator - Packs per outer box	12
EAN/UPC - Case	6941970603621

Dimensional drawing



Photometric data



Accent Lighting Spots - RS350 G2 RC Rd D75 7W 35K 36D 1H

Light Distribution Diagram - RS350 G2 RC Rd D75 7W 35K 36D 1H

Deep Recessed Spotlight

