Ref. Certif. No.

NL-126553

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic Controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☐ Additional information on page 2
Ratings and principal characteristics	**Product data** Ratings: Xi 15W/m 0.2-0.35A 42V DS S TD 230V Pin: 11/14/16/19 W; Uin: 220-240 V~; Iin: 0,05/0,06/0,07/0,08 A; fn: 50/60 Hz; PF: 0,93; Prated: 8,5/10,5/13/15 W; Uoutput: 30-42 Vdc, Uout: 60 Vdc; Irated: 0,2/0,25/0,3/0,35 A; ta: -20…+50 °C; tc: +80 °C; Built-in; SELV Xi 25W/m 0.45-0.6A 42V DS S TD 230V Pin: 24/26/29/31 W; Uin: 220-240 V~; Iin: 0,10/0,11/0,12/0,13 A; fn: 50/60 Hz; PF: 0,96; Prated: 19/21/23/25 W; Uoutput: 30-42 Vdc, Uout: 60 Vdc; Irated: 0,45/0,5/0,55/0,6 A; ta: -20…+50 °C; tc: +80 °C; Built-in; SELV Xi 36W/m 0.7-0.85A 42V DS S TD 230V Pin: 36/39/41/43 W; Uin: 220-240 V~; Iin: 0,16/0,17/0,18/0,18 A; fn: 50/60 Hz; PF: 0,96; Prated: 30/32/34/36 W; Uoutput: 30-42 Vdc, Uout: 60 Vdc; Irated: 0,7/0,75/0,8/0,85 A; ta: -20…+50 °C; tc: +80 °C; Built-in; SELV Xi 40W/m 0.9-1.05A 42V DS S TD 230V Pin: 46/48/48/48 W; Uin: 220-240 V~; Iin: 0,20/0,21/0,21/0,21 A; fn: 50/60 Hz; PF: 0,96; Prated: 38/40/40/40 W; Uoutput: 30-42 Vdc, Uout: 60 Vdc; Irated: 0,9/0,95/1/1,05 A; ta: -20…+45 °C; tc: +80 °C; Built-in; SELV
Trademark / Brand (if any)	XITANIUM, ADVANCE, PHILIPS or SIGNIFY

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-05

Signature: Caroline Chen

Ref. Certif. No.

NL-126553

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xi 15W/m 0.2-0.35A 42V DS S TD 230V, Xi 25W/m 0.45-0.6A 42V DS S TD 230V, Xi 36W/m 0.7-0.85A 42V DS S TD 230V and Xi 40W/m 0.9-1.05A 42V DS S TD 230V
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: AU, EU Group Differences, NZ
As shown in the Test Report Ref. No. which forms part of this Certificate	6271292.50(A-B) and 6271292.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-05

Signature: Caroline Chen