Australia and New Zealand Certificate of Suitability

Certificate
ULL-104548

Issue date
2026-06-23

Expiration date
2031-06-23

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic Controlgear for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability

Certificate No: ULL-104548
Date of Issue/Revision: 2026-06-23

Trade Name or Trademark: PHILIPS, SIGNIFY, XITANIUM, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:
Models and Ratings :
Xi 15W/m 0.2-0.35A 42V DS S TD 230V
Pin: 11/14/16/19 W, Uin: 220-240 V~, Iin: 0.05/0.06/0.07/0.08 A, fn: 50/60 Hz, PF: 0.93, Prated: 8.5/10.5/13/15 W, Uoutput: 30-42 Vdc. Uout: 60 Vdc, Irated: 0.2/0.25/0.3/0.35 A, ta: -20…+50 °C, tc: +80 °C,
Built-in, SELV

Xi 25W/m 0.45-0.6A 42V DS S TD 230V
Pin: 24/26/29/31 W, Uin: 220-240 V~, Iin: 0.10/0.11/0.12/0.13 A, fn: 50/60 Hz, PF: 0.96, Prated: 19/21/23/25 W, Uoutput: 30-42 Vdc. Uout: 60 Vdc, Irated: 0.45/0.5/0.55/0.6 A, ta: -20…+50 °C, tc: +80 °C,
Built-in, SELV

Xi 36W/m 0.7-0.85A 42V DS S TD 230V
Pin: 36/39/41/43 W, Uin: 220-240 V~, Iin: 0.16/0.17/0.18/0.18 A, fn: 50/60 Hz, PF: 0.96, Prated: 30/32/34/36 W, Uoutput: 30-42 Vdc. Uout: 60 Vdc, Irated: 0.7/0.75/0.8/0.85 A, ta: -20…+50 °C, tc: +80 °C,
Built-in, SELV

Xi 40W/m 0.9-1.05A 42V DS S TD 230V
Pin: 46/48/48/48 W, Uin: 220-240 V~, Iin: 0.20/0.21/0.21/0.21 A, fn: 50/60 Hz, PF: 0.96, Prated: 38/40/40/40 W, Uoutput: 30-42 Vdc. Uout: 60 Vdc, Irated: 0.9/0.95/1/1.05 A, ta: -20…+45 °C, tc: +80 °C,
Built-in, SELV

© 2026 UL LLC. All rights reserved.