



中国国家强制性产品认证证书

证书编号：2024011002613371

认证委托人名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产者名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产企业名称及地址

产品名称和系列、型号、规格

LED 模块用交流或直流电子控制装置（LED 控制装置，内装式，恒流模式，自耦式，不可调光，tc:85°C，定温热保护:110°C）
见附页。220-240V~50/60Hz，186-250VDC

产品标准和技术要求

GB 17625.1-2022;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合《强制性产品认证实施规则 照明电器》（CNCA-C10-01:2014）的要求，特发此证。

发证日期：2024 年 03 月 14 日 有效期至：2029 年 03 月 13 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

经中国合格评定国家认可委员会认可 CNAS C001-P



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024011002613371

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND LOCATION OF THE FACTORY

PRODUCT NAME, MODEL AND SPECIFICATION

A.C. & D.C. Supplied Electronic Controlgear For LED Modules (Built-in, Constant Current Mode,
Auto-wound Controlgear, Non-dimmable, tc:85°C, Temperature Declared Thermally Protected:110°C)
See Appendix. 220-240V ~ 50/60Hz , 186-250VDC

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009
This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

Valid from: Mar.14,2024

Valid until: Mar.13,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





中国国家强制性产品认证证书

证书编号：2024011002613371

证书附页：第 1 页 共 1 页

序号	产品型号	参数	拨码开关			
1.	Xitanium 150W 400-700mA 215V DS 230V EL	输入：220-240V ~ /186-250V 三 50/60Hz/DC , 0.75A/0.6-0.85A, λ : 0.9C; 输出：140-215V 三 , Max 300V 三	Prated	Irated	Pin1	Pin2
			86W	0.40A	ON	ON
			107.5W	0.50A	ON	OFF
			129W	0.60A	OFF	ON
			150W	0.70A	OFF	OFF
2.	Xitanium 100W 350-500mA 200V DS 230V EL	输入：220-240V ~ /186-250V 三 50/60Hz/DC , 0.5A/0.38-0.55A, λ : 0.9C; 输出：80-200V 三 , Max 250V 三	Prated	Irated	Pin1	Pin2
			70W	0.35A	ON	ON
			80W	0.40A	ON	OFF
			90W	0.45A	OFF	ON
			100W	0.50A	OFF	OFF
3.	Xitanium 90W 200-350mA 256V DS 230V EL	输入：220-240V ~ /186-250V 三 50/60Hz/DC , 0.43A/0.34-0.49A, λ : 0.9C; 输出：150-256V 三 , Max 300V 三	Prated	Irated	Pin1	Pin2
			51.2W	0.20A	ON	ON
			64W	0.25A	ON	OFF
			76.8W	0.30A	OFF	ON
			90W	0.35A	OFF	OFF
恒流输出, tc: 85°C, ∇ , 自耦式, 内装式						

本页为证书附页，应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司