



MASTER LED tube EM/Mains T8 with Recycled Plastic

MASTER LEDtube Starter EMP GenIII

Our new sustainability hero Philips MASTER LEDtube T8 EM/mains — a pioneering LED tube designed for performance, durability and environmental impact. As the first-ever LED tube to feature 40% post-consumer recycled plastic, it sets a new standard for sustainable lighting without compromising quality. With a long lifetime of 75,000 hours and high luminous efficacy up to 185 lm/W, the MASTER LEDtube T8 ensures outstanding energy efficiency. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low-energy consumption and an exceptionally long lifetime ensure that this tube masters every demanding application.

Product data

General Information		Input frequency	- Hz
Lighting Technology	LED	Voltage (nom.)	100-277 V
Warranty period	5 years	Controls and Dimming	
Light Technical		Dimmable	No
Colour Code	- [Not Specified]	Mechanical and Housing	
Colour designation	- [Not Specified]	Net Weight (Piece)	0.004 kg
Correlated Colour Temperature (Nom)	-	Approval and Application	
Colour consistency	-	Energy-saving product	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Approval marks	RoHS compliance CE marking
Operating and Electrical		CE mark	Yes
Line Frequency	- Hz		

MASTER LED tube EM/Mains T8 with Recycled Plastic

EU RoHS compliant	Yes
Product Data	
Order product name	MASTER LEDtube Starter EMP GenIII
Full product name	MASTER LEDtube Starter EMP GenIII
Full EOC	871951448537200
Order code	929003481702

Material no. (12 NC)	929003481702
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514485372
Numerator – packs per outer box	40
EAN/UPC - Case	8719514485396

