



**MASTER LEDtube Starter
EMP GenIII**

929003481702



For top performance and sustainability

Our new sustainability hero Philips MASTER LEDtube T8 EM/mains — a pioneering LED tube designed for performance, durability and environmental impact. As the first-ever LED tube to feature 40% post-consumer recycled plastic, it sets a new standard for sustainable lighting without compromising quality. With a long lifetime of 75,000 hours and high luminous efficacy up to 185 lm/W, the MASTER LEDtube T8 ensures outstanding energy efficiency. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low-energy consumption and an exceptionally long lifetime ensure that this tube masters every demanding application.

General Information

Lighting Technology	LED
Warranty period	5 years

Light Technical

Colour Code	- [Not Specified]
Colour designation	- [Not Specified]

Correlated Colour Temperature (Nom)	-
Colour consistency	-
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical

Line Frequency	- Hz
Input frequency	- Hz
Voltage (nom.)	100-277 V

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Net Weight (Piece)	0.004 kg
--------------------	----------

Approval and Application

Energy-saving product	Yes
Approval marks	RoHS compliance
CE mark	Yes
EU RoHS compliant	Yes

Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_929003481702_en_IE.txt	Download 
Environmental Product Declaration	Philips-Accessory-COMF-2167-Ref-929003481702-EPD.pdf	Download 

Product Data

Order product name	MASTER LEDtube Starter EMP GenIII
Full product name	MASTER LEDtube Starter EMP GenIII
Full EOC	871951448537200
Order code	929003481702
Material no. (12 NC)	929003481702
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8719514485372
Numerator – packs per outer box	40
EAN/UPC - Case	8719514485396