



# MASTER LED tube EM/Mains T8 with Recycled Plastic

## MASTER LEDtube Starter EMP GenIII

Our new sustainability hero Philips MASTER LEDtube T8 EM/mains — a pioneering LED tube designed for performance, durability and environmental impact. As the first-ever LED tube to feature 40% post-consumer recycled plastic, it sets a new standard for sustainable lighting without compromising quality. With a long lifetime of 75,000 hours and high luminous efficacy up to 185 lm/W, the MASTER LEDtube T8 ensures outstanding energy efficiency. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low-energy consumption and an exceptionally long lifetime ensure that this tube masters every demanding application.

### Product data

General Information		Input frequency	
Lighting Technology	LED		- Hz
Warranty period	5 years	Voltage (nom.)	100-277 V
Light Technical		Controls and Dimming	
Colour Code	- [Not Specified]	Dimmable	No
Colour designation	- [Not Specified]	Mechanical and Housing	
Correlated Colour Temperature (Nom)	-	Net Weight (Piece)	0.004 kg
Colour consistency	-	Approval and Application	
LLMF at end of nominal lifetime (nom.)	70 %	Energy-saving product	Yes
Operating and Electrical		Approval marks	RoHS compliance CE marking
Line Frequency	- Hz	CE mark	Yes

## MASTER LED tube EM/Mains T8 with Recycled Plastic

EU RoHS compliant	Yes
<b>Product Data</b>	
Order product name	MASTER LEDtube Starter EMP GenIII
Full product name	MASTER LEDtube Starter EMP GenIII
Full EOC	871951448537200
Order code	929003481702

Material no. (12 NC)	929003481702
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514485372
Numerator – packs per outer box	40
EAN/UPC - Case	8719514485396

