



# CorePro LED tube EM/ Mains T8



## CorePro LEDtube 1200mm 15.5W 865 T8 CL

CorePro, LEDtube, T8, EM/Mains, 1200 mm, 15.5 W, 36W TL-D, 6500 K, 1800 lm, CRI 80, 50000 hour(s)

Philips CorePro LEDtubes are the quick and easy way to replace T8 fluorescent or other LED tubes with a fast pay back time. Not only does the Core range of LEDtubes require a low initial investment, but LED energy efficiency also delivers instant savings that you can bank on over a long and reliable lifetime. Plus, with the same lamp size and light distribution as fluorescent alternatives, you'll never know the difference. There are two ways to install these LED tubes: Rewire your existing fluorescent-based luminaires so the CorePro LEDtubes work directly on the Mains. Or simply change the fluorescent starter to an LED starter that can be used with your Electromagnetic ballasts.

### Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.
- Installation must be done according to the installation diagrams provided with the lamp or available online. Installation must be done by a certified professional.

### Product data

General Information		Flux measurement reference	
Cap-Base	G13	Sphere	
Nominal lifetime	50,000 hour(s)	Light Technical	
Switching Cycle	200,000	Color Code	865 [CCT of 6500K]
Lighting Technology	LEDtube	Beam Angle (Nom)	240 degree(s)
		Luminous Flux	1,800 lm

# CorePro LED tube EM/Mains T8

Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	116 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0

## Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	15.5 W
Lamp Current (Nom)	84 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	36W TL-D
Inrush current at mains	5.08
Max. lamp no. on MCB B type 10A - Mains	91
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	91
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	24
Max. lamp no. on MCB B type 16A - Mains	145
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	145
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	38
Ballast Compatibility	EM/Mains

## Temperature

T-Case Maximum (Nom)	60 °C
----------------------	-------

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Bulb Finish	Frosted
-------------	---------

Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	T8
Net Weight (Piece)	0.220 kg

## Approval and Application

Energy Efficiency Class	E
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
EPREL Registration Number	1827703
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C

## Application Conditions

can it be used in closed luminaires	Yes
-------------------------------------	-----

## Product Data

Order product name	CorePro LEDtube 1200mm 15.5W 865 T8 CL
Full product name	CorePro LEDtube 1200mm 15.5W 865 T8 CL
Full product code	871951444809400
Order code	929003519862
Material Nr. (12NC)	929003519862
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514448094
Numerator - Packs per outer box	20
EAN/UPC - Case	8719514448100



# CorePro LED tube EM/Mains T8

## Dimensional drawing




Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 15.5W 865 T8 CL	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

## Photometric data



Light Distribution Diagram - CorePro LEDtube 1200mm 15.5W 865 T8 CL

Spectral Power Distribution Colour - CorePro LEDtube 1200mm 15.5W 865 T8 CL



Technical Drawing No. 01 Page Lighting 01 Page 1/1

General uniform lighting - CorePro LEDtube 1200mm 15.5W 865 T8 CL

# CorePro LED tube EM/Mains T8

## Lifetime




Lumen Maintenance Diagram - CorePro LEDtube 1200mm 15.5W 865 T8 CL

Life Expectancy Diagram



LifetimeVsTc

FailureRate



Lumen Maintenance Diagram - CorePro LEDtube 1200mm 15.5W 865 T8 CL

## CorePro LED tube EM/Mains T8

