

Classic filament LED bulbs

LED CLA 40W A60 B22 4000K CL EELA SRT AU

LEDbulb, A60, 40 W, B22, 4000 K, 485 lm, 50000 hour(s), Glass

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information		Photobiological safety according to EN 62471	
Cap-Base	B22	RG1	
Nominal lifetime	50,000 hour(s)		
Switching Cycle	50,000		
Rated Lifetime (Hours)	50,000 hour(s)		
Lighting Technology	LEDbulb		
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Input Frequency	50 to 60 Hz
Color Code	840 [CCT of 4000K]	Power Consumption	2.3 W
Luminous Flux	485 lm	Lamp Current (Nom)	30 mA
Color Designation	Cool White (CW)	Wattage Equivalent	40 W
Correlated Color Temperature (Nom)	4000 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	210 lm/W	Warm-up time to 60% light	0.5 s
Color Consistency	<6	Power Factor (Fraction)	0.4
Color rendering index (CRI)	80	Voltage (Nom)	220-240 V
LLMF At End Of Nominal Lifetime (Nom)	70 %	Temperature	
		T-Case Maximum (Nom)	35 °C

Classic filament LED bulbs

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Overall length	105 mm
Overall width	60 mm
Overall height	105 mm
Dimensions (Height x Width x Depth)	105 x 60 x 105 mm
Bulb Shape	A60
Net Weight (Piece)	0.036 kg

Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	UltraEfficient EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	LED CLA 40W A60 B22 4000K CL EELA SRT AU
Full product name	LED CLA 40W A60 B22 4000K CL EELA SRT AU
Full product code	871951445824600
Order code	929003539819
Material Nr. (12NC)	929003539819
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514458246
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514458253

Dimensional drawing



Product	D	C
LED CLA 40W A60 B22 4000K CL EELA SRT AU	60 mm	105 mm

Photometric data




Spectral Power Distribution Colour - LED CLA 40W A60 B22 4000K CL EELA SRT AU

General uniform lighting - LED CLA 40W A60 B22 4000K CL EELA SRT AU

Classic filament LED bulbs

Photometric data



Light Distribution Diagram - LED CLA 40W A60 B22 4000K CL EELA SRT AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED CLA 40W A60 B22 4000K CL EELA SRT AU

