



Classic filament LED bulbs

LED CLA 60W A60 B22 3000K CL EELA SRT AU

LEDbulb, A60, 60 W, B22, 3000 K, 840 lm, 50000 hour(s), Glass

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	B22
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	50,000 hour(s)
Lighting Technology	LEDbulb
Light Technical	
Color Code	830 [CCT of 3000K]
Color Code	830 [CCT of 3000K]
Luminous Flux	840 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	210 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Photobiological safety according to EN 62471 RG1	
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	45 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	35 °C
Controls and Dimming	
Dimmable	No

Classic filament LED bulbs

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Overall length	105 mm
Overall width	60 mm
Overall height	105 mm
Dimensions (Height x Width x Depth)	105 x 60 x 105 mm
Bulb Shape	A60
Net Weight (Piece)	0.036 kg


Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	UltraEfficient EyeComfort
Ambient temperature range	-20 to +45 °C

Product Data



Order product name	LED CLA 60W A60 B22 3000K CL EELA SRT AU
Full product name	LED CLA 60W A60 B22 3000K CL EELA SRT AU
Full product code	871951445826000
Order code	929003539919
Material Nr. (12NC)	929003539919
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514458260
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514458277

Dimensional drawing



Product	D	C
LED CLA 60W A60 B22 3000K CL EELA SRT AU	60 mm	105 mm

Photometric data




General uniform lighting - LED CLA 60W A60 B22 3000K CL EELA SRT AU

Spectral Power Distribution Colour - LED CLA 60W A60 B22 3000K CL EELA SRT AU

Classic filament LED bulbs

Photometric data




Light Distribution Diagram - LED CLA 60W A60 B22 3000K CL EELA SRT AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED CLA 60W A60 B22 3000K CL EELA SRT AU

