



CorePro LED tube EM/ Mains T8

CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT

CorePro, LEDtube, T8, EM/Mains, Single-end, 600 mm, 220-240 V, 8.8 W, 18W TL-D, 6500 K, 900 lm, 50000 hour(s)

Philips CorePro LEDtubes are the quick and easy way to replace T8 fluorescent or other LED tubes with a fast pay back time. Not only does the Core range of LEDtubes require a low initial investment, but LED energy efficiency also delivers instant savings that you can bank on over a long and reliable lifetime. Plus, with the same lamp size and light distribution as fluorescent alternatives, you'll never know the difference. There are two ways to install these LED tubes: Rewire your existing fluorescent-based luminaires so the CorePro LEDtubes work directly on the Mains. Or simply change the fluorescent starter to an LED starter that can be used with your Electromagnetic ballasts.

Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.
- Installation must be done according to the installation diagrams provided with the lamp or available online. Installation must be done by a certified professional.

Product data

General Information		Light Technical	
Cap-Base	G13	Color Code	865 [CCT of 6500K]
Nominal lifetime	50,000 hour(s)	Beam Angle (Nom)	240 degree(s)
Switching Cycle	200,000	Luminous Flux	900 lm
Lighting Technology	LEDtube	Color Designation	Cool Daylight
		Correlated Color Temperature (Nom)	6500 K

CorePro LED tube EM/Mains T8

Luminous Efficacy (rated) (Nom)	102 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471 RGO	

Operating and Electrical

Input Frequency	50 to 60 Hz
Power Consumption	8.8 W
Lamp Current (Nom)	46 mA
Wattage Equivalent	18 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	18W TL-D
Ballast Compatibility	EM/Mains

Temperature

T-Case Maximum (Nom)	50 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass

Product Length	600 mm
Bulb Shape	T8
Net Weight (Piece)	0.120 kg

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance KEMA Keur certificate
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT
Full product name	CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT
Full product code	872110303636000
Order code	929003547320
Material Nr. (12NC)	929003547320
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103036360
Numerator - Packs per outer box	10
EAN/UPC - Case	8721103036377


Dimensional drawing




Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

CorePro LED tube EM/Mains T8


Photometric data



Light Distribution Diagram - CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT



Spectral Power Distribution Colour - CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT




General uniform lighting - CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT

Lifetime




Life Expectancy Diagram




FailureRate

CorePro LED tube EM/Mains T8


Lifetime



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT



LifetimeVsTc



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT

