

Ecofit LED tubes T8

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm
Overall length	1,214 mm
Overall width	28 mm
Overall height	1,214 mm
Dimensions (Height x Width x Depth)	1214 x 28 x 1214 mm
Bulb Shape	T8
Net Weight (Piece)	0.175 kg

Approval and Application


Energy Saving Product	Yes
Approval Marks	RoHS compliance KEMA Keur certificate

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 °C to 45 °C

Product Data



Order product name	Ecofit E LEDtube 1200mm 18W 765 T8 I MY
Full product name	Ecofit E LEDtube 1200mm 18W 765 T8 I MY
Full product code	871951447542700
Order code	929003550837
Material Nr. (12NC)	929003550837
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514475427
Numerator - Packs per outer box	25
EAN/UPC - Case	8719514475434

Dimensional drawing



Product	D1	D2	A1	A2	A3
Ecofit E LEDtube 1200mm 18W 765 T8 I MY	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Photometric data




Spectral Power Distribution Colour - Ecofit E LEDtube 1200mm 18W 765 T8 I MY

General uniform lighting - Ecofit E LEDtube 1200mm 18W 765 T8 I MY


Ecofit LED tubes T8

Photometric data




Light Distribution Diagram - Ecofit E LEDtube 1200mm 18W 765 T8 I MY


Lifetime




Lumen Maintenance Diagram - Ecofit E LEDtube 1200mm 18W 765 T8 I MY



Life Expectancy Diagram




FailureRate



LifetimeVsTc

Ecofit LED tubes T8

Lifetime



Lumen Maintenance Diagram - Ecofit E LEDtube 1200mm 18W 765 T8 I MY

