



CorePro Plastic LED bulbs

CorePro LEDbulb ND 4.9-40W A60 E27 830

CorePro, LEDbulb, A60, 40 W, E27, 3000 K, 470 lm, CRI 80, 10000 hour(s), Plastic

The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides beautiful light and dependable performance you expect from LED at an affordable price. CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings of 80% and provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	10,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	2 years
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	180 degree(s)
Luminous Flux	470 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	95 lm/W


Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4.9 W
Lamp Current (Nom)	45 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.54

CorePro Plastic LED bulbs

Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60
Net Weight (Piece)	0.030 kg
Approval and Application	
Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	1218501
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per 1 EN 61000-3-3	

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 °C to 45 °C
Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	CorePro LEDbulb ND 4.9-40W A60 E27 830
Full product name	CorePro LEDbulb ND 4.9-40W A60 E27 830
Full product code	872016916911100
Order code	929003560908
Material Nr. (12NC)	929003560908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169169111
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169169128



Dimensional drawing



Product	D	C
CorePro LEDbulb ND 4.9-40W A60 E27 830	60 mm	107 mm


CorePro Plastic LED bulbs

Photometric data



General uniform lighting - CorePro LEDbulb ND 4.9-40W A60 E27 830

Light Distribution Diagram - CorePro LEDbulb ND 4.9-40W A60 E27 830




Spectral Power Distribution Colour - CorePro LEDbulb ND 4.9-40W A60 E27 830

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro LEDbulb ND 4.9-40W A60 E27 830

CorePro Plastic LED bulbs

