



# Ecofit LED tubes T8

## Ledtube DE E HO 1200mm 22W 740 T8

Entry, LEDtube, T8, Mains, Double-ended, 1200 mm, 220-240 V, 22 W, 36W TL-D, 4000 K, 2000 lm, 15000 hour(s)

Entry, LEDtube, T8, Mains, Double-ended, 1200 mm, 220-240 V, 22 W, LED alternative to 36W TL-D, 4000 K, 2000 lm, 15000 hour(s), 90 lm/W, G13, Beam angle 240 degree(s), Glass

### Product data

General Information	
Cap-Base	G13
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	740 [CCT of 4000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	2,000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<7
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz


Power Consumption	22 W
Lamp Current (Max)	150 mA
Lamp Current (Min)	150 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	36W TL-D
Ballast Compatibility	Mains
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm

# Ecofit LED tubes T8

Bulb Shape	T8
Net Weight (Piece)	0.180 kg
<b>Approval and Application</b>	
Energy Saving Product	Yes
Approval Marks	RoHS compliance
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C
<b>Application Conditions</b>	
Wireless Technology	Not applicable



<b>Product Data</b>	
Order product name	Ledtube DE E HO 1200mm 22W 740 T8
Full product name	Ledtube DE E HO 1200mm 22W 740 T8
Full product code	871951448592100
Order code	929003576138
Material Nr. (12NC)	929003576138
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514485921
Numerator - Packs per outer box	25
EAN/UPC - Case	8719514485938

## Dimensional drawing



Product	D1	D2	A1	A2	A3
Ledtube DE E HO 1200mm 22W 740 T8	25.5 mm	28 mm	1,197 mm	1,204 mm	1,212 mm

## Photometric data




General uniform lighting - Ledtube DE E HO 1200mm 22W 740 T8

Spectral Power Distribution Colour - Ledtube DE E HO 1200mm 22W 740 T8


# Ecofit LED tubes T8

## Photometric data




Light Distribution Diagram - Ledtube DE E HO 1200mm 22W 740 T8

## Lifetime




Life Expectancy Diagram



Lumen Maintenance Diagram - Ledtube DE E HO 1200mm 22W 740 T8


Life Expectancy Diagram



Lumen Maintenance Diagram - Ledtube DE E HO 1200mm 22W 740 T8

## Ecofit LED tubes T8

### Lifetime



### Life Expectancy Diagram

