



Ecofit LED tubes T8

Ledtube DE E HO 1200mm 22W 765 T8

Entry, LEDtube, T8, Mains, Double-ended, 1200 mm, 220-240 V, 22 W, 36W TL-D, 6500 K, 2000 lm, 15000 hour(s)

Entry, LEDtube, T8, Mains, Double-ended, 1200 mm, 220-240 V, 22 W, LED alternative to 36W TL-D, 6500 K, 2000 lm, 15000 hour(s), 90 lm/W, G13, Beam angle 240 degree(s), Glass

Product data

General Information	
Cap-Base	G13
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	765 [CCT of 6500K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	2,000 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<7
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz


Power Consumption	22 W
Lamp Current (Max)	150 mA
Lamp Current (Min)	150 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	36W TL-D
Ballast Compatibility	Mains
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm

Ecofit LED tubes T8

Bulb Shape	T8
Net Weight (Piece)	0.180 kg
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C
Application Conditions	
Wireless Technology	Not applicable



Product Data	
Order product name	Ledtube DE E HO 1200mm 22W 765 T8
Full product name	Ledtube DE E HO 1200mm 22W 765 T8
Full product code	871951448594500
Order code	929003576238
Material Nr. (12NC)	929003576238
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514485945
Numerator - Packs per outer box	25
EAN/UPC - Case	8719514485952

Dimensional drawing



Product	D1	D2	A1	A2	A3
Ledtube DE E HO 1200mm 22W 765 T8	25.5 mm	28 mm	1,197 mm	1,204 mm	1,212 mm

Photometric data




General uniform lighting - Ledtube DE E HO 1200mm 22W 765 T8

Spectral Power Distribution Colour - Ledtube DE E HO 1200mm 22W 765 T8


Ecofit LED tubes T8

Photometric data




Light Distribution Diagram - Ledtube DE E HO 1200mm 22W 765 T8

Lifetime




Life Expectancy Diagram



Lumen Maintenance Diagram - Ledtube DE E HO 1200mm 22W 765 T8

Life Expectancy Diagram



Life Expectancy Diagram

Ecofit LED tubes T8

