MASTER VALUE LED spot LV

MASTER LED 3.9-35W 3000K MR16 36D

LEDspot, MR16, 35 W, GU5.3, 3000 K, 280 lm, 25000 hour(s), Metal

LEDspot, MR16, 35 W, GU5.3, 3000 K, 280 lm, 25000 hour(s), Metal, 71 lm/W, RG1

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU5.3
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot

Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	280 lm
Luminous Intensity (Nom)	600 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	71 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

MASTER VALUE LED spot LV

Operating and Electrical	
Input Frequency	- Hz
Power Consumption	3.9 W
Lamp Current (Nom)	385 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V

Temperature	
T-Case Maximum (Nom)	68 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Metal
Bulb Shape	MR16
Net Weight (Piece)	0.028 kg

Approval and Application	
Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

Application Conditions	
Wireless Technology	Not applicable

Product Data	
Order product name	MASTER LED 3.9-35W 3000K MR16 36D
Full product name	MASTER LED 3.9-35W 3000K MR16 36D
Full product code	872016917452800
Order code	929003610508
Material Nr. (12NC)	929003610508
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169174528
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169174535

Dimensional drawing



Product	D	C
MASTER LED 3.9-35W 3000K MR16 36D	50.5 mm	50 mm

MASTER VALUE LED spot LV

Photometric data



Spectral Power Distribution Colour - MASTER LED 3.9-35W 3000K MR16 36D



Light Distribution Diagram - MASTER LED 3.9-35W 3000K MR16 36D



Accent Lighting Spots - MASTER LED 3.9-35W 3000K MR16 36D

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MASTER LED 3.9-35W 3000K MR16 36D

MASTER VALUE LED spot LV

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.