



# TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

## TForce ESS LED HB MV 4.5Klm 45W 865 E27

LED, T-shape T120, Mains only, 45 W, 75W CFL, 70W HID, E27, 6500 K, 4500 lm, 15000 hour(s)

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in Highbay application. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus they come for a low initial investment. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour rendering index enhance the lighting distribution while creating a comfortable, safe and high productivity environment.

### Warnings and Safety

• EM version requires an EM ballast to operate. Please refer to the installation guide or consult a Philips Lighting representative.

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED

Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	180 degree(s)
Luminous Flux	4,500 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K

## TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

### Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	45 W
Lamp Current (Nom)	356 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220–240 V
Wattage Equivalent (LED HID only)	75W CFL, 70W HID
Ballast Compatibility	Mains only

### Temperature

T-Case Maximum (Nom)	77 °C
----------------------	-------

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	T-shape T120
Net Weight (Piece)	0.142 kg


### Approval and Application

Energy Saving Product	Yes
Energy Consumption kWh/1000 h	45 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C

### Product Data

Order product name	TForce ESS LED HB MV 4.5Klm 45W 865 E27
Full product name	TForce ESS LED HB MV 4.5Klm 45W 865 E27
Full product code	872016919021400
Order code	929003632108
Material Nr. (12NC)	929003632108
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169190214
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169190221



### Dimensional drawing



Product	D	C
TForce ESS LED HB MV 4.5Klm 45W 865 E27	121 mm	199 mm


# TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

## Photometric data



General uniform lighting - TForce ESS LED HB MV 4.5Klm 45W 865 E27

Spectral Power Distribution Colour - TForce ESS LED HB MV 4.5Klm 45W 865 E27




Light Distribution Diagram - TForce ESS LED HB MV 4.5Klm 45W 865 E27

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - TForce ESS LED HB MV 4.5Klm 45W 865 E27

## TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

